


EndoNova

Brushless Endomotor With OGP
Mode

Lighter Design
Ledge Bypassing
Function
Lower Noise
5 Programs
16:1 Super Mini
Contra Angle



Advanced Endomotor for Confident Everyday Endodontics



Technical:

Adaptor working voltage AC100-240V 50/60HZ;


Adjustable torque, range 0.6-3.9N.cm

Rotation speed range: 100-1000rpm

Volume(mm) 130.2×23.4×20.5

Weight/PCS 67.4g


Packing material carton



16:1


Super-mini contra angle

Easily reach every treatment area
Contra angle speed ratio 16:1



100-1000rpm

The maximum speed can reach to 1000 rpm



5 Programs

P1~P3 : Memory program
P4 : Reciprocation program
P5 : OGP program



33dBA

104g

Lighter and Quieter

Reducing hand fatigue , give you the best feel
Improved motor , lower noise , allows you to better focus on treatment



OGP Mode

Special ledge bypassing function
safer and more convenient