


bestrongworld bestrongworld global.bestrong.com info@bestrong.com

# **Muscle Groups Focus**





#### Ab & Back Trainer 1900

The back muscle trainer is, as the name suggests, designed to develop the muscles of the back, while the abdominal muscle trainer does the opposite, working the muscles of the abdomen. Together, the two elements complement each other to effectively strengthen the core muscles.


#### **Attributes**

Product code	1-1-040
Certificate	EN 16630
Age group	14 + years
Capacity	2 people
Max. weight load	99 kg
Type	Fitness
Difficulty level	Easy

#### **QR** Code




### **Side View**



 $0.8 \, \text{m}^3$ 

 $0.8 \, \text{m}^3$ 

## **Plan View**



#### Installation information

Number of installers (concrete) At least 2 people Total installation time (concrete) 60-120 min. Number of installers (equipment) At least 2 people 30-60 min. Total installation time (equipment) Excavation volume Concrete volume 4pc 0,5 x 0,5 x 0,8 m Size of the base structure Anchoring options In-g
In combined structures, the volume of concrete required varies. In-ground or surface

## **Technical specification**

Safety surfice area Around 1,5 m radius Net weight 76 kg Material S235 Critic fall height 800 mm Color options

For more color options, discuss with your sales representative.

### Warranty

Structure Steel Paint Plastic Rubber Moving parts
Detailed information in the warranty document

10 years 5-10 years 2 years 5-10 years 1-3 years 2 years

# Material specification



The element is made of high quality S235 steel, which has been cleaned via sandblasting. A corrosion resistant powder coating finish is then applied. Also available with galvanized surface for even greater protection and longevity!




The seats and backrests are made of strong HDPE material. Which is fully heat, moisture and UV resistant.



The connecting ments are fastened with vandal-proof stainless steel screws and nuts.



The ends of the bars and posts are sealed with injection-moulded plastic caps.





The clamp system allows for easy assembly and extreme stability.







