

Ergo Endo Black



RC Plugger 0.5mm
MD 7011X REF

ErgoDentà

Ergo Endo **Black**

Endo Black is ErgoDenta's line of endodontic instruments made for precise root canal work. The matte black finish reduces light reflection, giving you a clearer view inside the tooth and helping you focus on small details that matter.

Designed with our ergonomic Danish approach, these instruments feel balanced and comfortable in the hand. They support steady finger control and good tactile feedback, which is especially important when working in narrow and delicate canals.

The Endo Black range covers the key steps of endodontic treatment — from examination and access to cleaning, shaping, and filling support. Each instrument is made from high-quality stainless steel and built to handle daily use and repeated sterilization.

Endo Black is about better visibility, better control, and smoother workflows during endodontic procedures.

Made for Modern Endodontics



Improved
Visibility



Ergonomic
Handling



Durable
Construction



Better
Control

Table of Contant

Endo Instruments



Gutta-Percha remover	04
Endo Plugger	05
Endo Spreader	05
Endo Explorers & Pluggers	06
Endo Spreader & Pluggers	06

Endo Mirrors

HD Mirrors	07
Microscopic Mirror	07



Rubberdam clamps



Anteriors	09
Upper Molars	09
Lower Molars	09
Pre molars	10
Molars / Universal	10

Rubberdam kit

Rubberdam kit	11
---------------	----




Endo Surgery Instruments



Scissor in Black	12
Tweezers in Black	13
Apicoectomy Retractor	14
Endo Forceps	14
Endo Tweezers	14

Gutta-Percha **Remover**



Hook, Remove & Move On!

The ultra-thin 0.4 mm tip preserves canal walls. The double-ended design offers versatile hooks and easy retrieval from any angle, leaving no residue.

7001 X

Gutta Percha Remover, Up-Down, 0.4mm Hook



7002 X



Gutta Percha Remover, Left-Right, 0.4mm Hook



Endo Instruments


Endo Plugger

Used for condensing gutta-percha, providing a dense and secure canal filling.



Endo Spreader

Designed to laterally compact gutta-percha, creating space for additional filling material for a superior seal



Endo Instruments

Excavator



Excavator 31L 8080 X
Excavator 32L 8081 X
Excavator 33L 8082 X

Endo Spreader & Pluggers




Ø0.4mm & Ø0.4mm 7056-KX
Ø0.4mm & Ø0.6mm 7057-KX
Ø0.6mm & Ø0.8mm 7058-KX
Ø0.6mm & Ø1.0mm 7059 X

Periodontal Probe



Periodontal CP 12/15 8020 X

Endo Explorer



Explorer 17/17L 8000 X
Explorer KX1, straight 8001 X
Explorer KX2, angled 8002 X
Endo Explorer 7050-KX
Root Canal Explorer 7051-KX

Endo Curette



Curette Lucas 85 7104K-X

Periosteal Elevator



Periosteal Prichard 7160 SP

Round Scalpel



Handle No:3 8041 X

HD Mirrors in box

Mirror handle **9315**



Ø22mm
1514HK

Ø24mm
1515HK



Microscopic mirrors

36-layer coated, anti-glare mirror for clear visibility in microscope-assisted procedures. Available in two thicknesses: ultra-thin 0.7mm for maximum access and visibility, and standard 1.5mm for added durability. Sold with the ErgoLite mirror handle.

Size	Regular	Ultrathin
3mm	7091R	7091U
5mm	7092R	7092U
7mm	----	7095U
2x7mm	7093R	----
3x6mm (Oval)	----	7093U
3x6mm (WaterDrop)	----	7094U
3x9mm	7094R	----



Ultrathin
0.7mm



Regular
1.5mm



Precision Vision for Endodontics

Sharper Details

Confident Endo Work

Better Control

Black-coated

Rubberdam Clamps



Provide reduced *Glare* for
improved *Visibility* during procedures.


Black-coated Rubberdam Clamps

Provide reduced glare for improved visibility during procedures.


Available in Gold, Blue, Black and Silver coatings.
More details on our website or general catalog.




Anteriors




Upper Molars



Lower Molars



Pre molars



Using Rubber Dam Clamps Effectively


Successful rubber dam isolation depends on selecting and placing the correct clamp for each clinical situation. A properly fitted clamp provides stable tooth isolation, supports moisture control, and helps create a clear, dry working field.

Clamps should always be inspected before use and reprocessed according to standard sterilization protocols. Correct positioning below the tooth's height of contour ensures reliable retention throughout the procedure, while proper adaptation helps avoid unnecessary pressure on gingival tissues.

Choosing the right clamp design and size improves procedural efficiency, enhances visibility, and contributes to patient comfort during restorative and endodontic treatments.



Molars / Universal



Rubberdam instruments



2711

Brewer Rubberdam
Clamp Forceps



2712

Strocke Rubberdam
Clamp Forceps



2715

Ivory Rubberdam
Clamp Forceps



2740

Ivory Rubberdam
Punch Forceps



2741

Ainsworth Rubberdam
Punch Forceps



2761

Rubber Dam Clamp
Organizing Board for 12



2750

Rubber Dam
Stand Small

2753

Rubber Dam
Stand Large



5513

Sterilization
Cassette

Rubber Dam Kit


9917K

Rubberdam clamps

K2703-W8A	Universal: W8A
K2705-W8	Universal: W8
K2701-212	Anterior: #212
K2701-9	Anterior molars: #9
K2704-W2	Premolars: W2
K2704-2	Premolars: #2
K2704-2A	Premolars: 2A
K2702-W7	Lower jaw molars: W7
K2701-00	Lower jaw molars #00
K2702-W3	Lower jaw molars: W3
K2702-12A	Lower jaw molars : 12A
K2705-30	Upper jaw molars: #30

Rubberdam instruments & accessories

2740	Ivory Rubber Dam Punch
2715	Ivory Rubber Dam Clamp Forcep 17cm
2761	Rubber Dam Clamp Organizing Board for 12
2750	Rubber Dam Stand Small
2753	Rubber Dam Stand Large
5513	Sterilization cassette



All-in-one kit with everything you need for quick and accurate rubber dam placement. The kit is available with standard, gold or black clamps

Scissors in Black

Experience sharp, accurate cutting with Super-cut scissors featuring a durable black coating.

- Matte coating to reduce glare
- Optimized for surgical precision
- Easy to clean surface
- Long lasting sharpness
- Razor edge

TC
+
SC
Super Cut



Goldman Fox

13cm
Straight
3007-4S

13cm
Curved
3007-4C



La-Garange

11.5 cm
Double Curved
3008-4D



Iris

11.5cm
Straight
3002-4S

11.5 cm
Curved
3002-4C



Metzenbaum
Stump

14.5cm
Curved
3011-4C

Tweezers in **Black**

Experience precise, secure grip with Super-grip tweezers featuring a durable black coating.



Perry



3621-3C
13cm
Curved

Meriam Tweezer



3636-3A
16cm
Serrated, Fig 1.



3636-4A
16cm
Serrated, Fig 1. TC

College Tweezer



3627-3A
15cm
Serrated



3628-3A
15cm
Short Serrated




3630-3A
15cm
Serrated, with Lock

Micro Surgical Tweezer



3802-3G
18cm
Straight



3802-3CG
18cm
Curved



3802-3
18cm
Straight,
Anatomic



3801-3G
15cm
Straight

Gerald



3671-3G
17cm
Straight



3671-3CG
17cm
Curved

Endo Tweezers

— with lock —



3676-1A

Endo tweezers,
serrated handle
15cm, Curved



3677-1A

Endo tweezers
smooth handle
15cm, Curved



3667-1

DeBaKey
Tweezers
16cm, Straight



7452S

Endo File
Cleaner Round
Shape, Sky Blue

Apicoectomy Retractor



45°
Angled

4180

Apicoectomy
retractor, toothed,
45° angled



90°
Angled

4181

Apicoectomy
retractor, toothed,
90° angled

Endo Forceps



7411

Angled Endodontic
Forceps, 14cm



60°
Angled

7416

Root Fragment
Forceps - Long 60°



3209-2S

Needle holder
Micro-Vascular with
TC inserts

Ergo Endo **Black**

SCAN
ME!



ErgoDenta

ErgoDenta ApS

📍 Hørskættens 14, 2630 Taastrup | Denmark

☎ Tel. +45 5524 1100

🌐 www.ergodenta.dk | info@ergodenta.dk

RC Plugger 0.5mm
[MD] 7011 X [REF]